

[See all 14 Products in Family](#)

LightPath 354059 | 6.33mm Dia., 0.19 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-694** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

₹7,062

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,062 each
Qty 11-49	₹6,213 each
Need More?	Request Quote

Product Downloads

General	
354059	Lightpath Lens Code:
Aspheric Lens	Type:

Physical & Mechanical Properties	
6.33 ±0.015	Diameter (mm):

5.20	Clear Aperture CA (mm):
1.73	Edge Thickness ET (mm):
2.35 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties	
14.00 @ 633nm	Effective Focal Length EFL (mm):
0.19	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
633	Aspheric Design Wavelength (nm):
BBAR (600-1050nm)	Coating:
R _{abs} <1.0% @ 600 - 1050nm	Coating Specification:
60-40	Surface Quality:
2.63	f#:
600 - 1050	Wavelength Range (nm):
12.600	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.145	Transmitted Wavefront Error (λ, RMS):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Compact, Molded Aspheric Lens Design
- Improved Performance Compared to Doublet and Triplet Lenses
- Ideal for Laser Tools and Measurement Systems

LightPath® Laser Tool Molded Aspheric Lenses are designed to fulfill the needs of a variety of tools and measurement systems utilizing laser diodes, including leveling lasers, projectors, scanners, trackers, and gun sights. By utilizing a single aspheric lens, the need for a multi-lens system is eliminated, allowing for a more compact and robust design. Each aspheric lens is offered with various anti-reflection coatings for optimum transmission in the visible and NIR wavelength ranges. LightPath® Laser Tool Molded Aspheric Lenses’ anti-reflection coating options for each lens provides <1% average reflection over the entire design wavelength range. The lenses are offered in four different diameters: 3mm, 4.70mm, 6mm, and 6.33mm.

