

**TECHSPEC® 0.4 OD 12.5mm Diameter, Reflective ND Filter**



Stock **#64-128** 10 TO 12 DAYS

- 1 + **₹2,958.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹2,958.00                     |
| Qty 6+                        |
| ₹2,349.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
12.50

Angle of Incidence (°):  
0

Optical Density OD (Average):  
0.4

|                                                                                                                   |
|-------------------------------------------------------------------------------------------------------------------|
| <b>Substrate:</b> <br>Float Glass |
| <b>Coating:</b><br>Surface 1: Inconel                                                                             |
| <b>Reflection (%)</b> :<br>25.00                                                                                  |
| <b>Surface Quality</b> :<br>80-50                                                                                 |
| <b>Thickness (mm)</b> :<br>1.60 Nominal                                                                           |
| <b>Transmission (%)</b> :<br>40.00                                                                                |
| <b>Type</b> :<br>Neutral Density Filter                                                                           |
| <b>Blocking Wavelength Range (nm)</b> :<br>400 - 700                                                              |
| <b>Dimensional Tolerance (mm)</b> :<br>±0.5                                                                       |
| <b>Clear Aperture (%)</b> :<br>80                                                                                 |
| <b>Neutrality</b> :<br>±5% of Optical Density                                                                     |
| <b>Note</b> :<br>Optical density values are average over specified blocking wavelength range.                     |
| <b>Surface Flatness (P-V)</b> :<br>4 - 6λ                                                                         |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |