

0.40 NA, 6.25mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYAMolded Glass Aspheric Lenses

Stock **#13-586** 10 TO 12 DAYS

⊖ 1 ⊕ **₹8,265.00**

ADD TO CART

Qty 1-10
₹8,265.00
Qty 11+
₹6,525.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
6.38 +0.00/-0.02

Effective Focal Length EFL (mm):
6.25 @ 780nm

Numerical Aperture NA:
0.40

Substrate:  M-LaF81
Aspheric Design Wavelength (nm): 780
Coating: BBAR (680-880nm)
Coating Specification: Ravg <1% @ 680 - 880nm (typical)
Center Thickness CT (mm): 2.50
f#: 0.98
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 680 - 880
Working Distance (mm): 4.57
Conjugate Distance: 0
Transmitted Wavefront, RMS @ 632.8nm: 0.04λ
Model Number: AH11_Z

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View