

[See all 2 Products in Family](#)

## 0.42 NA, 6.5mm FL, RPO IR Molded Glass Aspheric Lens



Stock #73-679 **20+ In Stock**

- 1 + MRP ₹13,621

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹13,621 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Aspheric Lens **Type:**

#### Physical & Mechanical Properties

7.20 ±0.025 **Diameter (mm):**

3.33 **Clear Aperture CA (mm):**

4.47 **Center Thickness CT (mm):**

Protective as needed **Bevel:**

## Optical Properties

6.50 **Effective Focal Length EFL (mm):**

0.42 **Numerical Aperture NA:**

IG6 **Substrate:**

BBAR (800-1200) **Coating:**

**Coating Specification:**  
R<sub>avg</sub> <1% @ 800 - 1200, 0 - 30° AOI

80-60 **Surface Quality:**

0.9 **f#:**

800 - 1200 **Wavelength Range (nm):**

4.72 **Working Distance (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Precision Infrared Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Constructed with IG6 Infrared Glass Substrates

Rochester Precision Optics (RPO) Infrared Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Infrared Molded Glass Aspheric Lenses are available with 4.00 and 6.50mm focal lengths and are AR coated for >99% transmission from 800 - 1200nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.

**Note:** Use of this substrate at elevated temperatures (>150C) or in the presence of some acids/bases can lead to formation of toxic compounds and should be avoided. Please see MSDS for details.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools