

[See all 4 Products in Family](#)

0.26 NA, 11.0mm FL, RPO VIS Molded Glass Aspheric Lens



Stock #73-654 **20+ In Stock**

- 1 + MRP ₹9,383

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹9,383 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

7.20 ±0.015 **Diameter (mm):**

5.50 **Clear Aperture CA (mm):**

5.00 **Center Thickness CT (mm):**

Bevel:

Protective as needed

Optical Properties

11.00 **Effective Focal Length EFL (mm):**

0.26 **Numerical Aperture NA:**

D-K59 **Substrate:** □

633 **Aspheric Design Wavelength (nm):**

BBAR (400 - 600nm) **Coating:**

R_{avg} <1% @ 400 - 600nm **Coating Specification:**

60-40 **Surface Quality:**

1.53 **f#:**

400 - 600 **Wavelength Range (nm):**

7.97 **Working Distance (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Precision Visible Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Multiple Glass Substrates Available

Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses are available with various focal lengths and numerical apertures and are AR coated for >99% transmission from 400 - 600nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.