

[See all 14 Products in Family](#)

LightPath 354171 | 4.7mm Dia., 0.30 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-709** 20+ In Stock

[Other Coating Options](#)

-

1

+

₹5,985

ADD TO CART

Volume Pricing	
Qty 1-10	₹5,985 each
Qty 11-49	₹5,265 each
Need More?	Request Quote

Product Downloads

General	
354171	Lightpath Lens Code:
Aspheric Lens	Type:
Physical & Mechanical Properties	
4.70 ±0.015	Diameter (mm):

3.70	Clear Aperture CA (mm):
2.88	Edge Thickness ET (mm):
3.48 ±0.05	Center Thickness CT (mm):

Protective as needed	Bevel:
----------------------	--------

Optical Properties

6.20 @ 633nm	Effective Focal Length EFL (mm):
0.30	Numerical Aperture NA:

D-ZK3	Substrate: ☐
±1	Focal Length Tolerance (%):

633	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:

R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
80-50	Surface Quality:

1.67	f#:
350 - 700	Wavelength Range (nm):

4.100	Working Distance (mm):
Infinite	Conjugate Distance:

< 0.070	Transmitted Wavefront Error (λ, RMS):
---------	---------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Compact, Molded Aspheric Lens Design
- Improved Performance Compared to Doublet and Triplet Lenses
- Ideal for Laser Tools and Measurement Systems

LightPath® Laser Tool Molded Aspheric Lenses are designed to fulfill the needs of a variety of tools and measurement systems utilizing laser diodes, including leveling lasers, projectors, scanners, trackers, and gun sights. By utilizing a single aspheric lens, the need for a multi-lens system is eliminated, allowing for a more compact and robust design. Each aspheric lens is offered with various anti-reflection coatings for optimum transmission in the visible and NIR wavelength ranges. LightPath® Laser Tool Molded Aspheric Lenses' anti-reflection coating options for each lens provides <1% average reflection over the entire design wavelength range. The lenses are offered in four different diameters: 3mm, 4.70mm, 6mm, and 6.33mm.

