

LightPath 355375 | 6.51mm Dia., 0.30 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-131** **20+ In Stock**

[Other Coating Options](#)

-

1

+

₹6,075

ADD TO CART

Volume Pricing	
Qty 1-10	₹6,075 each
Qty 11-49	₹5,400 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Thickness: 0.250 (t) (mm)
Material: BK7


Compatible Window:

355375	Lightpath Lens Code:
Aspheric Lens	Type:
Collimate or Focus Laser Light	Typical Applications:
Physical & Mechanical Properties	
6.51 ±0.020	Diameter (mm):
4.54	Clear Aperture CA (mm):
2.71	Edge Thickness ET (mm):
3.19 ±0.04	Center Thickness CT (mm):
Protective as needed	Bevel:
5.151	Distance from Window to Lens (D) (mm):
Optical Properties	
7.50 @780nm	Effective Focal Length EFL (mm):
0.3	Numerical Aperture NA:
D-ZLaF52LA	Substrate: □
±1	Focal Length Tolerance (%):
780	Aspheric Design Wavelength (nm):
BBAR (1050-1600nm)	Coating:
R _{abs} <1.0% @ 1050 - 1600nm	Coating Specification:
40-20	Surface Quality:
1.67	f/#:
1050 - 1600	Wavelength Range (nm):
5.8	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.05	Transmitted Wavefront Error (λ, RMS):
Environmental & Durability Factors	
≤200	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



TECHNICAL INFORMATION

