

[See all 156 Products in Family](#)

TECHSPEC® 0.5" Dia. Protected Silver, $\lambda/10$ Flat Fused Silica



Stock #43-319-577 **17 In Stock**

1 MRP ₹12,107

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹12,107 each
Qty 11-25	₹10,796 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Flatness is specified as Peak to Valley **Note:**

Physical & Mechanical Properties

Diameter (mm):

12.70 +0.0/-0.5

3.20 ±0.8

Thickness (mm):

Commercial Polish

Back Surface:

11.43

Clear Aperture CA (mm):

Optical Properties

0.45 - 10

Wavelength Range (µm):

Metal

Coating Type:

Protected Silver (450-10000nm)

Coating:

λ10

Surface Flatness (P-V):

450 - 10000

Wavelength Range (nm):

Fused Silica (Corning 7980)

Substrate: □

R_{avg} >98% @450 - 2000nm
R_{avg} >98% @2000 - 10,000nm

Coating Specification:

60-40

Surface Quality:

0.5 J/cm² @ 532nm & 1064nm, 10ns

Damage Threshold, Reference: □

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 247:

United States

Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Fused Silica and ZERODUR® Substrates
- λ10 and λ20 Surface Flatness
- Variety of Coating Options Offered

TECHSPEC® Precision Optical Flat Mirrors are ideal for various applications, including interferometry, imaging systems, laser applications, optical path folding, and autocollimation. These mirrors are available in multiple coating and substrate options and surface flatness options of λ10 and λ20. The first substrate option ZERODUR®, a yellow-tinted glass ceramic, features an extremely low coefficient of thermal expansion. TECHSPEC® Precision Optical Flat Mirrors are ideal for applications where temperature fluctuation is a concern using the ZERODUR® substrate. The second option, Fused Silica, is optically clear and features excellent resistance to abrasion and high durability, making it the best choice for applications in harsh environments. Please note, calibration certificates are not supplied with these parts.

TECHSPEC® λ10 and λ20 Precision Optical Flats are available for testing and measurement applications.

Note: Surface flatness specifications are measured before coating.

Coating Curves

Compatible Mounts

