

TECHSPEC® 0.5X - 1.0X M Series Non-Telecentric Lens



Stock #87-535 **3 In Stock**

- 1 + MRP ₹64,782

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹64,782 each
Need More?	Request Quote

Product Downloads

General

Variable Magnification Lens **Type:**
Non-Telecentric, Variable Magnification **Style:**

Physical & Mechanical Properties

Variable **Iris Option:**

76.00	Length (mm):
30	Maximum Diameter (mm):
87	Weight (g):
0	Maximum Rear Protrusion (mm):
76	Maximum Length (mm):
56	Minimum Length (mm):

Optical Properties

Field of View at Max Sensor Format:	
Horizontal: 17.4 - 8.8mm - 7.8°	
Vertical: 13.0 - 6.7mm - 5.8°	
Diagonal: 27.7 - 11.1mm - 9.7°	
75 lp/mm @ >20%	Resolution:
11.00	Maximum Image Circle (mm):
0.0559	Numerical Aperture NA, Object Side:
5 (4)	Number of Elements (Groups):
<0.1	Typical Distortion @ 588nm (%):
0.5X - 1.0X	Primary Magnification PMAG:
61.5 - 100.1	Working Distance (mm):
FOV @ Max Sensor Format, H x V (mm):	
17.6 x 13.2 - 8.8 x 6.6	
f/4 - f/22	Aperture (f/#):
Coating Specification:	
M4 MgF ₂ @ 550nm	
22.56	Entrance Pupil Position (mm):
13.59	Object Space Principal Plane (mm):
-16.06	Image Space Principal Plane (mm):
0.08	Maximum Distortion (%):
-8.74	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
------	-------------------------------

Threading & Mounting

M25.5 x 0.50 (Female)	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	REACH 201:
View	Certificate of Conformance:
China	Country of Origin:
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038	

Product Details

- Variable Magnification Lens
- Up to 5 MegaPixels, 3.45m Pixel Size Sensors
- $\frac{2}{3}$ " C-Mount Lens

TECHSPEC® M Series Variable Magnification Lenses are designed for applications that may require constant adjustment of a system's field of view. Each lens provides a range of magnifications that users can adjust or lock down with a set screw. With coverage for up to $\frac{2}{3}$ " format sensors, these lenses feature compact, C-mount compatible designs for easy system integration. TECHSPEC® M Series Variable Magnification Lenses also include an adjustable iris to control light throughput and improve image quality. These lenses are ideal for use in high magnification machine vision and factory automation.

Note: Customized magnification versions are also available to meet volume requirements. Please contact technical support to discuss your specific requirements.

Technical Information

