

**TECHSPEC® 0.5X, 65mm WD, In-Line CompactTL™ Telecentric Lens**



65mm WD, 0.5X, In-Line Version (Left) and MS Version (Right)



Stock **#67-310** **4 In Stock**

⊖ 1 ⊕ ₹56,637

**ADD TO CART**

Volume Pricing	
Qty 1+	₹56,637 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

CompactTL™ Series **Series:**

Edmund Optics® **Manufacturer:**

Telecentric Lens **Type:**

**Compatible Light Guide/Source:**  
1/4" (0.312") and 1/8" (0.187")

In-Line Illumination      Type of Illumination:

## Physical & Mechanical Properties

Fixed      Iris Option:

89.98      Length (mm):

89.98      Length excluding Threads (mm):

32.00      Maximum Diameter (mm):

87      Weight (g):

## Optical Properties

17.6mm      Horizontal Field of View, 2/3" Sensor:

12.8mm      Horizontal Field of View, 1/2" Sensor:

9.6mm      Horizontal Field of View, 1/3" Sensor:

11.00      Maximum Image Circle (mm):

0.028      Numerical Aperture NA, Object Side:

±1      Working Distance Tolerance (mm):

6 (4)      Number of Elements (Groups):

0.052      Typical Telecentricity @ 588nm (°):

0.0304      Typical Distortion @ 588nm (%):

0.5X      Primary Magnification PMAG:

0.50      Telecentric Lens Magnification:

65      Working Distance (mm):

17.6 x 13.2      FOV @ Max Sensor Format, H x V (mm):

f/9      Aperture (f/#):

M4 MgF<sub>2</sub>      Coating:

±1.85mm (20% @ 20 lp/mm)      Depth of Field (mm):

0.5X      Magnification:

VIS      Lens Wavelength Range:

## Sensor

2/3"      Maximum Sensor Format:

4.50      Pixel Size (µm):

## Threading & Mounting

M29.5 x 0.5 (Female)      Filter Thread:

C-Mount      Mount:

## Regulatory Compliance

[Compliant](#)      RoHS 2015:

[View](#)      Certificate of Conformance:

[Compliant](#)      REACH 241:


China      Country of Origin:

## Product Details


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


## Technical Information




#67-310, 0.5X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Distortion Plot




#67-310, 0.5X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Relative Illumination Plot



#67-310, 0.5X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Telecentricity Plot



#67-310, 0.5X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 65mm Working Distance, f9



#67-310, 0.5X, 65mm WD, In-Line CompactTL™ Telecentric Lens, Depth of Field Plot, 65mm Working Distance, f9