

# 0.4 OD, 50mm Sq., Precision Anti-Reflection (AR) Coated Absorptive ND Filter



Precision Absorptive Neutral Density (ND) Filters

Stock **#16-054** 10 TO 12 DAYS

- 1 + **₹18,705.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| ₹18,705.00                    |
| Qty 11+                       |
| ₹16,530.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

**Dimensions (mm):**  
50.00 x 50.00 +0.00/-0.25

**Optical Density OD (Average):**  
0.4 ±10% @ 550nm

**Glass/Filter Number:**  
[SCHOTT NG11](#)

**Substrate:** ☐

|                                                                          |
|--------------------------------------------------------------------------|
| ND Filter Glass                                                          |
| <b>Length (mm):</b><br>50.00                                             |
| <b>Coating:</b><br>BBAR (450-700nm)                                      |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.50                     |
| <b>Surface Quality:</b><br>80-50                                         |
| <b>Transformation Temperature (°C):</b><br>481                           |
| <b>Thickness (mm):</b><br>3.78 (nominal)                                 |
| <b>Transmission (%):</b><br>39.81                                        |
| <b>Type:</b><br>Neutral Density Filter                                   |
| <b>Width (mm):</b><br>50.00                                              |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700                      |
| <b>Clear Aperture (%):</b><br>90                                         |
| <b>Transmitted Wavefront, P-V:</b><br>$\lambda/4$                        |
| <b>Parallelism (arcsec):</b><br><30                                      |
| <b>Coating Specification:</b><br>$R_{avg} \leq 1.0\%$ @ 450 - 700nm @ 0° |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |