

0.6 OD M49.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-735** CLEARANCE **1 In Stock**

-

1

+

₹2,786

ADD TO CART

Volume Pricing	
Qty 1+	₹2,786 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter	Type:
AR Coating: MgF ₂	Note:

Physical & Mechanical Properties

45.0	Clear Aperture CA (mm):
5.00	Thickness with Mount (mm):

Optical Properties	
0.6	Optical Density OD (Average):
ND Filter Glass	Substrate: □
80-50	Surface Quality:
25	Transmission (%):
400 - 700	Blocking Wavelength Range (nm):
R _{avg} ≤1.75% @ 400 - 700nm	Coating Specification:
Threading & Mounting	
M49 x0.75	Filter Thread:
3.8 ±0.1	Mount Thickness (mm):
51.0 +0/-0.2	Mount Diameter (mm):
6.3	Mount Thickness Including Threads (mm):
Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

- Spectrally Flat from 400-700nm
- Homogeneous Glass: Blocks by Absorption
- Light/Exposure Control for Imaging

Mounted Absorptive Neutral Density (ND) Filters appear gray in color and reduce the amount of light reaching the camera's sensor. Since the transmission value only varies over a small percentage in the visible, there is no effect on color balance. Instead of just stopping down the lens aperture due to high light levels, ND filters allow for wider apertures which can be used to decrease the depth of field. This allows the important information to be separated from the background. Mounted Absorptive Neutral Density (ND) Filters, compared to polarizing filters, are ideal for overall light reduction in cases of extreme light intensity. By stacking filters, it is possible to achieve other Optical Density (OD) values. All mounted filters can be threaded together with identical male and female threads on each mount. Optical Density exhibits an additive relationship; for example, stacking filters with OD values of 0.6 and 0.9 yields a resultant density of 1.5. The Optical Density (OD) is related to the transmission by the following equation: $T = 10^{-D} \times 100 = \text{percent transmission}$.

Technical Information

