

LightPath 355561 | 15mm Dia., 0.60 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-107** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹6,786.00**

ADD TO CART

Qty 1-10
₹6,786.00
Qty 11+
₹5,960.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
15.00 ±0.015

Effective Focal Length EFL (mm):
10.00 @ 850nm

Numerical Aperture NA:
0.6

Substrate: D-ZLaF52LA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 850
Coating: BBAR (1050-1600nm)
Coating Specification: R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality: 60-40
Clear Aperture CA (mm): 12.5
Edge Thickness ET (mm): 2.56
Center Thickness CT (mm): 5.38 ±0.05
f/#: 0.83
Bevel: Protective bevel as needed
Lightpath Lens Code: 355561
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 1050 - 1600
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 7
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant