

[See all 4 Products in Family](#)

0.55 NA, 5.30mm FL, RPO VIS Molded Glass Aspheric Lens



Stock #73-658 **7 In Stock**

- 1 + MRP ₹13,721

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹13,721 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

7.33 +0/-0.020 **Diameter (mm):**

5.83 **Clear Aperture CA (mm):**

2.93 **Center Thickness CT (mm):**

Bevel:

Protective as needed

Optical Properties

Effective Focal Length EFL (mm):

5.30

Numerical Aperture NA:

0.55

Substrate:

H-ZLaF52

Aspheric Design Wavelength (nm):

633

Coating:

BBAR (400 - 600nm)

Coating Specification:

R_{avg} <1% @ 400 - 600nm

Surface Quality:

60-40

f/#:

0.72

Wavelength Range (nm):

400 - 600

Working Distance (mm):

3.59

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Precision Visible Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Multiple Glass Substrates Available

Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Visible Molded Glass Aspheric Lenses are available with various focal lengths and numerical apertures and are AR coated for >99% transmission from 400 - 600nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.