

[See all 77 Products in Family](#)

LightPath 354140 | 2.4mm Dia., 0.58 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-615** **20+ In Stock**

[Other Coating Options](#)

-

1

+

₹6,075

ADD TO CART

Volume Pricing	
Qty 1-10	₹6,075 each
Qty 11-49	₹5,400 each
Need More?	Request Quote

Product Downloads

General

354140

Lightpath Lens Code:

Aspheric Lens

Type:

Collimate or Focus Laser Light

Typical Applications:

Physical & Mechanical Properties

2.40 ±0.015	Diameter (mm):
1.6	Clear Aperture CA (mm):
0.48	Edge Thickness ET (mm):
1.02 ±0.03	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties

1.45 @ 780nm	Effective Focal Length EFL (mm):
0.58	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
780	Aspheric Design Wavelength (nm):
BBAR (1050-1600nm)	Coating:
R _{abs} <1.0% @ 1050 - 1600nm	Coating Specification:
40-20	Surface Quality:
0.86	f/#:
1050 - 1600	Wavelength Range (nm):
0.81	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.07	Transmitted Wavefront Error (λ, RMS):

Environmental & Durability Factors

≤200	Operating Temperature (°C):
------	-----------------------------


Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information

