

TECHSPEC® 0.5X, 2/3" GoldTL™ Telecentric Lens



#54-798 (0.5X)

Stock **#54-798** **2 In Stock**

- 1 + MRP ₹2,06,787

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,06,787 each
Need More?	Request Quote

Product Downloads

General

GoldTL™ Series **Product Family:**

Stock No. of Mounting Clamp:
#56-025 Sold Separately

Telecentric Lens **Type:**

Focusable Telecentric **Special Type of Lens:**

Physical & Mechanical Properties

Fixed	Iris Option:
150.00	Length (mm):
150.00	Length excluding Threads (mm):
65.00	Maximum Diameter (mm):
0.84	Weight (kg):

Optical Properties

17.6mm	Horizontal Field of View, 2/3" Sensor:
14.4mm	Horizontal Field of View, 1/1.8" Sensor:
12.8mm	Horizontal Field of View, 1/2" Sensor:
9.00	Maximum Image Circle (mm):
0.042	Numerical Aperture NA, Object Side:
>55% @ 40 lp/mm	Resolution, Image Space MTF @ f/10:
8 (5)	Number of Elements (Groups):
<0.025	Typical Telecentricity @ 588nm (°):
0.015	Typical Distortion @ 588nm (%):
0.5X	Primary Magnification PMAG:
0.50	Telecentric Lens Magnification:
117 - 142	Working Distance (mm):
17.6 x 13.2	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/25	Aperture (f#):
M4 MgF ₂	Coating:
±2.1 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.5X	Magnification:
VS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting

M58 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:

Regulatory Compliance


View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details


- High Resolution Telecentric Lens for Measurement and Gauging
- Up to 5 MegaPixels, 3.45µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.06X to 1X

TECHSPEC® GoldTL™ Telecentric Lenses were designed specifically for machine vision and metrology applications. The unique focusable design allows for working distance adjustment, while still providing <math><0.2^\circ</math> telecentricity. These lenses also feature high resolutions, low distortions, and are available for 1/2" or 2/3" sensors. TECHSPEC® GoldTL™ Telecentric Lenses have a front filter thread for easy integration of [color filters](#), [polarizers](#) or other mounted components. Both the iris and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.


Technical Information




#54-798, 0.5X 2/3" GoldTL™ Telecentric Lens, Distortion Plot




#54-798, 0.5X 2/3" GoldTL™ Telecentric Lens, Relative Illumination Plot




#54-798, 0.5X 2/3" GoldTL™ Telecentric Lens, Telecentricity Plot




#54-798, 0.5X 2/3" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 130mm Working Distance, f6



#54-798, 0.5X 2/3" GoldTL™ Telecentric Lens, Depth of Field Plot, 130mm Working Distance, f6



#54-798, 0.5X 2/3" GoldTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 130mm Working Distance, f10



#54-798, 0.5X 2/3" GoldTL™ Telecentric Lens, Depth of Field Plot, 130mm Working Distance, f10

Stock No.	A	B	C	D	E	F	G
#56-024	88mm	16mm	34mm	94mm	120mm	101.6mm	50mm
#56-025	85mm	17.5mm	32.5mm	91mm	120mm	101.6mm	48.5mm
#56-026	103mm	—	39.5mm	107mm	103mm	90mm	55.5mm
#56-027	134mm	—	55mm	148mm	134mm	122mm	81mm