

[See all 20 Products in Family](#)

TECHSPEC® 0° AOI, 12.5mm Diameter, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-433** [CONTACT US](#)

- 1 + MRP ₹5,095

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹5,095 each
Qty 10-25	₹4,590 each
Qty 26-49	₹4,364 each
Need More?	Request Quote

Product Downloads

General

Cold Mirror **Type:**

Physical & Mechanical Properties

12.50 **Diameter (mm):**

Thickness (mm):

1.10 ±0.2

Dimensional Tolerance (mm):

+0.0/-0.2

Optical Properties

Longpass Filter **Transmission (%)**:

Dielectric **Coating Type**:

Cold Mirror, 0° **Coating**:

4 - 6λ **Surface Flatness (P-V)**:

400 - 1150 **Wavelength Range (nm)**:

BOROFLOAT® **Substrate**: □

0 **Angle of Incidence (°)**:

Coating Specification:
R_{avg} ≥95% @ 400 - 690nm and T_{avg} ≥90% @ 750 - 1200nm
AR Coating: R_{avg} <1% @ 700 - 1150nm

80-50 **Surface Quality**:

Regulatory Compliance

Compliant **RoHS 2015**:

View **Certificate of Conformance**:

Compliant **Reach 247**:

United States **Country of Origin**:



Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information



Quote Your Size

Compatible Mounts

;