


0° AOI 25mm Dia, Cold Mirror



Stock #43-844 CLEARANCE **20+ In Stock**

MRP ₹1,539

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,539 each
Need More?	Request Quote

Product Downloads

General

Cold Mirror **Type:**

Physical & Mechanical Properties

25.00 **Diameter (mm):**

3.30 **Thickness (mm):**

±0.25 **Dimensional Tolerance (mm):**

Optical Properties

Dielectric **Coating Type:**

Cold Mirror, 0° **Coating:**

4 - 6λ **Surface Flatness (P-V):**

425 - 1200 **Wavelength Range (nm):**

BOROFLOAT® **Substrate:** □

0.00 **Angle of Incidence (°):**

Coating Specification:
R_{avg} >90% @ 425 - 675nm
T_{avg} >85% @ 800 - 1200nm

80-50 **Surface Quality:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**



Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 0° and 45° Angle of Incidence Options Available
- Reflects 90% of Visible Light
- Transmits 80% of the NIR and IR

These Cold Mirrors have a 0° and 45° angle of incidence and are ideal for decreasing the undesirable heat caused by infrared radiation. A multi-layer dielectric coating reflects 90% of visible light while transmitting over 80% of the NIR and IR. Cold Mirrors function satisfactorily with resistance to damage from ambient temperatures of -45°C to +232°C and are ideal for projection systems, where heat build-up can lead to system damage. Made of BOROFLOAT® glass, these Cold Mirrors can be cut to the desired size for any application.

Technical Information



Compatible Mounts