

TECHSPEC[®] 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens



110mm WD, 0.75X, In-Line Version (Left) and VIS Version (Right)



Stock **#67-304** 1 In Stock

-

1

+

₹55,593

ADD TO CART

Volume Pricing	
Qty 1+	₹55,593 each
Need More?	Request Quote

Product Downloads

General	
CompactTL™ Series	Series:
Edmund Optics®	Manufacturer:
Telecentric Lens	Type:
Compatible Light Guide/Source: 1/4" (0.312") and 1/8" (0.187")	


In-Line Illumination		Type of Illumination:
Physical & Mechanical Properties		
Fixed		Iris Option:
160.01		Length (mm):
160.01		Length excluding Threads (mm):
29.5		Maximum Diameter (mm):
120		Weight (g):
Optical Properties		
11.7mm		Horizontal Field of View, 2/3" Sensor:
8.5mm		Horizontal Field of View, 1/2" Sensor:
6.4mm		Horizontal Field of View, 1/3" Sensor:
11.00		Maximum Image Circle (mm):
0.028		Numerical Aperture NA, Object Side:
±1		Working Distance Tolerance (mm):
5 (5)		Number of Elements (Groups):
0.061		Typical Telecentricity @ 588nm (°):
0.0212		Typical Distortion @ 588nm (%):
0.75X		Primary Magnification PMAG:
0.75		Telecentric Lens Magnification:
110		Working Distance (mm):
11.7 x 8.8		FOV @ Max Sensor Format, H x V (mm):
f/13.3		Aperture (f/#):
λ/4 MgF ₂		Coating:
±1.2mm (20% @ 20 lp/mm)		Depth of Field (mm):
0.75X		Magnification:
VIS		Lens Wavelength Range:
Sensor		
2/3"		Maximum Sensor Format:
4.50		Pixel Size (µm):
Threading & Mounting		
M25.5 x 0.50 (Female)		Filter Thread:
C-Mount		Mount:
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		REACH 241:
China		Country of Origin:

Product Details


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


Technical Information




#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Distortion Plot



#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Relative Illumination Plot



#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Telecentricity Plot



#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f13.3



#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f13.3