

[See all 48 Products in Family](#)

Norland Optical Adhesive NOA 170F, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 170F, 1 oz. Application Bottle, #14-794

Stock **#14-794** **4 In Stock**

⊖ 1 ⊕ MRP ₹28,674

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹28,674 each
Qty 5-11	₹25,807 each
Qty 12+	₹24,522 each
Need More?	Request Quote

Product Downloads

General	
1	Size (oz):
170F	Norland Number:
4 months	Shelf Life:

Bottle **Type:**

Typical Applications:
High refractive index adhesive for bonding glass or plastics. More flexible than NOA 170. Contains nanoparticles.

UV/MS **Cure:**

Optical Properties

1.70 @ 589nm **Index of Refraction (n_d):**

315 - 450 **Absorption Range (nm):**

Material Properties

Excellent **Glass Bonding:**

Good **Metal Bonding:**

Excellent **Plastic Bonding:**

800 - 900 **Viscosity (cps):**

Glass to Glass **Bonding Type:**

6 **Energy for Full Cure (J/cm^2):**

Environmental & Durability Factors

Soft & Flexible **Durability:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 251:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES

Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.