

[See all 17 Products in Family](#)

**TECHSPEC® 1000 - 1060nm, 12.7mm Dia., Ultrafast Mirror**



Stock #14-845 **20+ In Stock**

- 1 + MRP ₹22,701

**i** Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹22,701 each                  |
| Qty 10+        | ₹19,976 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Laser Mirror **Type:**

Yb:doped Lasers 1st Harmonic **Typical Applications:**

**Physical & Mechanical Properties**

80 **Clear Aperture (%):**

**Back Surface:**

Commercial Polish

12.70 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.10 **Thickness (mm):**

<10 **Parallelism (arcsec):**

## Optical Properties

10-5 **Surface Quality:**

**Coating Specification:**  
R<sub>s</sub> >99.95% @ 1000 - 1060nm  
R<sub>p</sub> >99.9% @ 1000 - 1060nm

**GDD Specification:**  
0 ±20fs<sup>2</sup> @ 1000 - 1060nm (s-pol & p-pol)

1000 - 1060 **Wavelength Range (nm):**

λ/8 **Surface Flatness (P-V):**

Dielectric **Coating Type:**

Ultrafast (1000-1060nm) **Coating:**

1030 **Design Wavelength DWL (nm):**

45 **Angle of Incidence (°):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

**Damage Threshold, By Design:**   
0.45 J/cm<sup>2</sup> @ 1030nm, 207fs, 1 pulse  
0.35 J/cm<sup>2</sup> @ 1030nm, 207fs, 1,000 pulses

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Lithuania **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


## Product Details

- Designed with High Reflectivity for Ultrafast Beam Steering
- Ion-Beam Sputtered Coating for Low Scatter and Absorption
- GDD as Low as 0±20fs<sup>2</sup> at Design Wavelength Range

TECHSPEC® High Performance Low GDD Ultrafast Mirrors are designed to have high reflectivity at 0° or 45° angles of incidence, making them ideal for ultrafast laser beam steering applications. These mirrors have a dispersion compensating coating obtained through a precision ion beam sputtering (IBS) process, providing lower scatter and absorption than traditional dielectric laser mirrors. TECHSPEC High Performance Low GDD Ultrafast Mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. Typical applications include use in the transport of femtosecond laser pulses.

**Note:** Please [contact us](#) if your application requires a TECHSPEC High Performance Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

## Technical Information



## Compatible Mounts