


# 1000µm Aperture Diameter, Gold-Plated Copper Aperture



Gold-Plated Copper Aperture

Stock **#39-905** **1 In Stock**

-

1

+

₹7,922

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹7,922 each                   |
| Qty 6-10       | ₹6,990 each                   |
| Qty 11+        | ₹6,462 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| Physical & Mechanical Properties |                               |
|----------------------------------|-------------------------------|
| 9.5                              | Outer Diameter (mm):          |
| Gold-Plated Copper               | Construction:                 |
| 1000                             | Fixed Aperture Diameter (µm): |
| 0.07 Nominal                     | Thickness (mm):               |

|                                     |                             |
|-------------------------------------|-----------------------------|
| ±5                                  | Aperture Tolerance (%):     |
| ±125                                | Aperture Centration (µm):   |
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 247:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Ceramic, Copper, Gold-Plated Copper, Molybdenum, or Tungsten Substrates
- Withstand High Power Densities up to 130MW/cm<sup>2</sup> (For Mo and W Substrates)
- Ideal for Spatial Filtering and Laser Aperturing

High Power Apertures are available in an assortment of available substrates, making them a versatile option for a variety of laser applications. These products are ideal for spatial filtering and as a general aperture. The apertures have an outer diameter of 3/8" (9.5mm). High Power Apertures have one shiny side for high reflectivity while the other is blackened for absorption. The ceramic apertures are white on both sides. The aperture's thickness and the materials' high reflectivity enable them to withstand and quickly dissipate increased irradiation from high-energy lasers. Densities as high as 100MW/cm2 (130MW/cm2 for molybdenum and Tungsten substrates) have been used without damage to the apertures.