

[See all 98 Products in Family](#)

100µm Aperture Diameter, 1" OD Mounted, Gold-Plated Copper Aperture



Stock #90-374 **NEW** 2 In Stock

1 MRP ₹13,317

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹13,317 each
Qty 6+	₹11,854 each
Need More?	Request Quote

Product Downloads

General

Mounted **Type:**

Physical & Mechanical Properties

25.4 +0.000/-0.05 **Outer Diameter (mm):**

Construction:

Gold-Plated Copper

100 **Fixed Aperture Diameter (µm):**

0.07 Nominal **Thickness (mm):**

±5 **Aperture Tolerance (%):**

±125 **Aperture Centration (µm):**

Threading & Mounting

2.54 **Mount Thickness (mm):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ceramic, Copper, Gold-Plated Copper, Molybdenum, or Tungsten Substrates
- Withstand High Power Densities up to 130MW/cm² (For Mo and W Substrates)
- Ideal for Spatial Filtering and Laser Aperturing

High Power Apertures are available in an assortment of available substrates, making them a versatile option for a variety of laser applications. These products are ideal for spatial filtering and as a general aperture. The apertures have an outer diameter of 3/8" (9.5mm). High Power Apertures have one shiny side for high reflectivity while the other is blackened for absorption. The ceramic apertures are white on both sides. The aperture's thickness and the materials' high reflectivity enable them to withstand and quickly dissipate increased irradiation from high-energy lasers. Densities as high as 100MW/cm² (130MW/cm² for molybdenum and Tungsten substrates) have been used without damage to the apertures.