

TECHSPEC[®] 100mm Dia., 0.63 Numerical Aperture VIS Coated, Aspheric Lens



Stock #22-709 10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹91,350.00

ADD TO CART

Qty 1-5
₹91,350.00
Qty 6+
₹73,080.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
100.00 +0.0/-0.1

Effective Focal Length EFL (mm):
80.00 @ 587.6nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 61.35
Substrate: N-SF5
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤1.5% @ 425 - 675nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 90
Edge Thickness ET (mm): 5.78
Center Thickness CT (mm): 31.20 ±0.1
f#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 12.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant