

[See all 9 Products in Family](#)

100 x 150mm, Red, EuroBrite™ Spot Light

See More by [Advanced Illumination](#)



Red AI EuroBrite Spot Light

Stock **#33-454** 1 In Stock

-

1

+

₹75,600

ADD TO CART

Volume Pricing	
Qty 1+	₹75,600 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
50,000	Operating Lifetime (hours):
SL-S100150M625	Model Number:

LED Illuminator	Type of Illumination:
See Technical Information Tab for Typical Intensity	

Advanced Illumination	Manufacturer:
Spot Light	Geometry:
Strobed or Constant	Illumination Mode:
Physical & Mechanical Properties	
150 x 139 x 30	Dimensions (mm):
253.00	Weight (g):
100 x 150	Active Area (mm):
Optical Properties	
Red	Color:
625	Wavelength (nm):
Electrical	
0.42 - 0.49A	Maximum Input Current:
10% @ 0.7V, 100% @ 10V	Analog Intensity Control:
10µm	Trigger-to-Pulse Latency:
Hardware & Interface Connectivity	
Flying Leads	Connector:
24V nominal (min. 22 / max 28)	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Environmental & Durability Factors	
0 - 60	Operating Temperature (°C):
IP67	Environmental Rating:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Daisy Chain up to Four 100 x 150mm Units
- Requires No Heat Sink
- Available in White, Red, and Blue

Advanced Illumination EuroBrite™ Spot Light illuminators feature on-board smart drivers functional during strobe and continuous operation modes making them ideal for the most demanding performance constraints. Adaptive OverDrive™ allows for power optimization while in strobing mode, and Adaptive Thermal Feedback™ gives operational current control to the user, preventing overheating and eliminating the need for a heat sink. These Advanced Illumination EuroBrite™ Spot Light illuminators feature a ruggedized, sealed enclosure, and are available in white, red, or blue versions. The ability to operate four 100 x 150mm units connected to one another, and an analog dimming control operable in both strobe and continuous modes add to illuminator’s customizability.

Note: A 24V power supply is required.

Technical Information

Typical Intensity				
Size	50 x 75mm	50 x 75mm	50 x 75mm	100 x 150mm
Working Distance	100mm	300mm	600mm	600mm
Area	79 x 56mm	117 x 99mm	ø198mm	325 x 198mm
Typical Irradiance (W/m²)	100.0	74	28	147
Typical Illuminance (kLux)	34.0	25	10	49
