

[See all 12 Products in Family](#)

1000mm Travel, Belt Driven Motorized Linear Stage

See More by [Zaber™](#)



Stock #22-235 **1 In Stock**

- 1 + MRP ₹2,65,846

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,65,846 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**

Yes **Encoder:**

Yes **Manual Control/ LED Indicators:**

Zaber Technologies Inc. **Manufacturer:**

Note:

Requires a 24-48 VDC power supply and either [#15-295](#) for USB connectivity or [#15-297](#) for RS-232 connectivity. A data cable ([#15-296](#) or [#15-299](#)) can be used to daisy chain multiple stages together to control simultaneously.

2-Phase Stepper **Type of Motor:**

Rotary Quadrature Encoder **Encoder Type:**

Motor Installation Guide:
Motor Installation and Setup Guide can be found [here](#)

Physical & Mechanical Properties

Linear (X) **Type of Movement:**

Recirculating Ball Linear Guide **Guide System:**

1150 x 134 **Stage Size (mm):**

1000 **Travel (mm):**

925 **Accuracy (μm):**

< 250 **Backlash (μm):**

76 **Height (mm):**

50 **Load Capacity (kg):**

< 20 **Repeatability (μm):**

3000 (Maximum) **Speed (mm/s):**

90 **Thrust (N):**

3.625 **Weight (kg):**

400 CPR **Encoder Resolution:**

Optical Properties

7.03125 **Resolution (μm):**

Electrical

3500 **Maximum Operating Current (mA):**

Hardware & Interface Connectivity

Synchronous Belt **Type of Drive:**

Power Supply:
Power Supply Required and Sold Separately:
USA: [#15-294](#)
Europe: [#15-294](#)
Japan: [#23-662](#)
Korea: [#33-773](#)
China: [#15-294](#)

USB with [#15-295](#)
RS-232 with [#15-297](#) **Computer Interface:**

Environmental & Durability Factors

0 - 50 **Operating Temperature ($^{\circ}\text{C}$):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Canada **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor, **Imported By:**

Product Details

- Designed for Use with Most 40mm T-Slot Extrusion Framing Systems and Accessories
- 500mm and 1000mm Long Travel Lengths Available
- Controlled Manually or via RS-232 Serial Interface
- Integrated 400 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ T-Slot Extrusion Belt Driven Stages are computer-controlled stages based on a modular, expandable, T-Slot extrusion structure. The stages are compatible and easily integrated with most T-Slot extrusion framing systems. Zaber™ T-Slot Extrusion Belt Driven Stages can be controlled by the [Zaber™ Programmable Joystick Controller](#) (sold separately), a computer using an optional RS-232 or USB data cable, or manually with the knob integrated into the motor unit. The stage mounting platforms include 6XM4 x0.7 mounting holes on a 25mm grid. Each stage features rotary quadrature encoders integrated into the stepper motor, with 400 Counts per Revolution (CPR) encoder resolution. The integrated rotary encoder provides closed-loop control and slip/stall detection and recovery.

Note: 24-48 VDC universal power supply (required), data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories.
