

TECHSPEC® 10.0mm Dia. x 15.0mm FL, Uncoated, Plano-Convex Lens



Stock #63-472 10 TO 12 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **₹2,436**

ADD TO CART

Qty 1-9

₹2,436

Qty 10+

₹2,197

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Effective Focal Length EFL (mm):

15.00 @ 587.6nm

Back Focal Length BFL (mm):

13.32

Coating:

Uncoated

Substrate:

[NSF11](#)

Surface Quality:

40-20

Power (P-V) @ 632.8nm:

1.5λ

Irregularity (P-V) @ 632.8nm:

λ/4

Focal Length Tolerance (%):

±1

Centering (arcmin):

<1

Center Thickness CT (mm):

3.00 ±0.05

Edge Thickness ET (mm):

1.89

Radius R₁ (mm):

11.77

Clear Aperture CA (mm):

9

f#:

1.5

Numerical Aperture NA:

0.33

Type:

Plano-Convex Lens

Bevel:

Protective bevel as needed

Wavelength Range (nm):

400 - 2500

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 219:

[Compliant](#)

Certificate of Conformance:

[View](#)
