

[See all 8 Products in Family](#)

## 100mm Dia x 19mm FL Alum. Coated, Parabolic Reflector



Stock #68-791 **2 In Stock**

1  MRP ₹40,961

 Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹40,961 each                  |
| Qty 11-25      | ₹36,119 each                  |
| Qty 26-49      | ₹34,001 each                  |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

#### General

Parabolic Mirror **Type:**

#### Physical & Mechanical Properties

100.00 +0.0/-0.5 **Diameter (mm):**

30.0 **Center Hole Diameter (mm):**

|                                    |  |
|------------------------------------|--|
| 32.0                               | <b>Height (mm):</b>                        |
| <b>Optical Properties</b>          |  |
| Metal                              | <b>Coating Type:</b>                       |
| Protected Aluminum (400-700nm)     | <b>Coating:</b>                            |
| 400 - 700                          | <b>Wavelength Range (nm):</b>              |
| <a href="#">BOROFLOAT®</a>         | <b>Substrate:</b> <input type="checkbox"/> |
| 0.190                              | <b>Aperture (f#):</b>                      |
| R <sub>avg</sub> >85% @400 - 700nm | <b>Coating Specification:</b>              |
| 19.00                              | <b>Focal Length FL (mm):</b>               |

|   |                                    |
|---|------------------------------------|
| <b>Regulatory Compliance</b>  |                                    |
| <a href="#">View</a>  | <b>Certificate of Conformance:</b> |
| Japan   | <b>Country of Origin:</b>          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | <b>Imported By:</b>                |


## Product Details

- Precision Polished Substrate
- Protected Aluminum and Cold Mirror Coating Options
- Ideal for Highly Divergent Light Sources
- [Precision Ellipsoidal Reflectors](#) Also Available


Precision Parabolic Reflectors are ideal for collimating a light source placed at the focal point of the mirror. The parabolic profile eliminates spherical aberration, allowing the light source to maintain its wavefront characteristics. These Precision Parabolic Reflectors feature very low *f*/#s, making them ideal for highly divergent light sources. The protected aluminum coating features broadband high reflection through the visible and IR spectra. The cold mirror coating reflects visible light while transmitting NIR, making it ideal for cold condensing applications.

Precision Parabolic Reflectors are precision polished, yielding exact aspheric profiles. These mirrors offer improved thermal stability and superior focusing efficiency versus commercially available press-molded reflectors. Typical applications include use as steppers for PCB, LCD, or PDP production, solar simulators, fiber optic illuminators, and projectors.

## Technical Information



| Diameter | Focal Length f | Center Hole Diameter d | Height H | Stock No.               |
|----------|----------------|------------------------|----------|-------------------------|
| 100mm    | 12.5mm         | —                      | 45mm     | <a href="#">#90-964</a> |
|          |                |                        |          | <a href="#">#90-967</a> |
|          | 19mm           | 30mm                   | 32mm     | <a href="#">#68-791</a> |
|          |                |                        |          | <a href="#">#68-795</a> |
| 152mm    | 17mm           | 30mm                   | 79mm     | <a href="#">#68-792</a> |
|          | 30mm           | 35mm                   | 47mm     | <a href="#">#90-965</a> |
| 220mm    | 100mm          | —                      | 33mm     | <a href="#">#68-793</a> |
| 300mm    | 42mm           | —                      | 130mm    | <a href="#">#90-966</a> |



;