

100mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-179 CLEARANCE 1 In Stock

-

1

+

₹49,760

ADD TO CART

Volume Pricing	
Qty 1+	₹49,760 each
Need More?	Request Quote

Product Downloads

General

Type:

F-Theta Lens

Physical & Mechanical Properties

Maximum Diameter (mm):

87

Flange Distance (mm):

126.9

Input Beam Diameter, 1/e² (mm):

12

Maximum Length (mm):

Optical Properties	
101.60	Focal Length FL (mm):
±22.68	Scan Angle (°):
56.5 x 56.5	Scan Field (mm):
Not Specified	Telecentricity (°):
≥95	Transmission (%):
107.9	Working Distance (mm):
1064	Design Wavelength DWL (nm):
1064	Wavelength Range (nm):
17	Focus Size Diameter, 1/e ² (µm):

Threading & Mounting	
M85 x 1.0	Mounting Threads:

Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ideal for Laser Scanning Applications
 - Diffraction Limited Across the Scan Field with Low Wavefront Error
 - Long Working Distances and Large Scan Areas
 - [Galvanometers](#), [Beam Expanders](#), and [Laser Sources](#) Also Available
- Edmund Optics® F-Theta Lenses are designed to provide flat fields at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta Lenses feature compact form factors, offer a wide range of focal lengths up to 273mm, and large scan fields up to 164mm (X) x 164mm (Y). Optimized for common fiber laser sources and Nd:YAG fundamental or second harmonic, these lenses are available in design wavelengths of 532nm and 1064nm with common mounting threads for easy integration into galvo systems. Edmund Optics® F-Theta Lenses are a cost-effective solution for laser scanning and laser processing applications including laser marking, engraving, cutting, drilling, and 3D modeling.