

[See all 8 Products in Family](#)

## 100mm<sup>2</sup> DUV Photodiode with Ceramic Housing



DUV Photodiodes

Stock **#84-986** [CONTACT US](#)

1 [-](#) [+](#) MRP ₹23,576

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹23,576 each
Qty 5-9	₹20,921 each
Qty 10-24	₹18,479 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

3 @ 0 V, 1 kΩ **Rise Time (μs):**

### Physical & Mechanical Properties

10.0 x 10.0 **Size of Active Area (mm):**

**Active Area (mm<sup>2</sup>):**

100.0

## Optical Properties

980.00 **Peak Response Wavelength (nm):**

## Electrical

0.5 **Responsivity @ 980nm (AW):**

Minimum: 0.04  
Typical: 0.2 **Shunt Resistance @ V=-10mV (GΩ):**

0.34 **Responsivity @ 633nm (AW):**

0.12 **Responsivity @ 200nm (AW):**

1100.00 **Capacitance @ V<sub>R</sub>=0V (pF):**

$8.2 \times 10^{-14}$  **Noise Equivalent Power NEP (W/ Hz<sup>1/2</sup>):**  
@ 0 V, 200nm

5.00 **Maximum Reverse Voltage (V):**

## Hardware & Interface Connectivity

Ceramic **Connector:**

## Environmental & Durability Factors

-20 to +60 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.