

100μm 0.22 NA VIS/NIR Fiber, 10m Length



Stock **#57-085** 10 TO 12 DAYS

-

1

+

₹4,263.00

ADD TO CART

Qty 1-4

₹4,263.00

Qty 5+

₹3,741.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Acceptance Angle (°):
25.4

Buffer Material:
Polyimide

Cladding Diameter (μm):
110 ±3

Coating: VS/NIR
Minimum Bend Radius (mm): 22/11 (Continuous/Momentary)
Substrate: Fused Silica (Corning 7980)
Length (m): 10.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 124 ±3
Core Diameter (µm): 100 ±3
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.440
Wavelength Range (nm): 300 - 2400
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View