

TECHSPEC® 101.6 x 101.6mm, Enhanced Aluminum, 4-6λ Mirror



Stock #18-926 10 TO 12 DAYS

⊖ 1 ⊕ **₹4,698**

ADD TO CART

Qty 1-5

₹4,698

Qty 6+

₹3,698

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):

4 - 6λ

Substrate:

Float Glass

Surface Quality:

60-40

Dimensions (mm):

101.60 x 101.60 +0.00/-0.25

Coating Specification:

R_{avg} ≥95% @ 450 - 650nm @ 45°

Coating:

Enhanced Aluminum (450-650nm)

Coating Type:

Metal

Clear Aperture CA (mm):

91.44 x 91.44

Edges:

Seamed, 0.5mm Maximum Edge Chip

Thickness (mm):

3.00 (nominal)

Type:

Flat Mirror

Wavelength Range (nm):

450 - 650

Length (mm):

101.60

Width (mm):

101.60

Damage Threshold, By Design:

0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)
