

[See all 1 Products in Family](#)

1025-1095nm 25.4mm Dia. Laser Non-Polarizing Beamsplitter



Laser Line Non-Polarizing Plate Beamsplitters

Stock **#33-036** **6 In Stock**

MRP ₹43,888

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹43,888 each
Qty 6-25	₹34,706 each
Need More?	Request Quote

Product Downloads

General

Non-Polarizing Beamsplitter **Type:**

Physical & Mechanical Properties

<0.25mm x45° **Bevel:**

>90 **Clear Aperture (%):**

Plate	Construction:
25.40 +0.0/-0.1	Diameter (mm):
<1	Parallelism (arcmin):
5.00 ±0.1	Thickness (mm):

Optical Properties

45	Angle of Incidence (°):
Back Surface: AR Coating	Coating:
$R_{\text{abs}} < 0.75\%$ @ 1025 - 1095nm	Coating Specification:
<5	Polarization Separation (Rs-Rp) (%):
50/50	Reflection/Transmission Ratio (R/T):
50 ±5	Reflectivity (Rs%, Rp%):
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
λ/8	Surface Flatness (P-V):
20-10	Surface Quality:
1025 - 1095	Wavelength Range (nm):
>1 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design: <input type="checkbox"/>
λ/8	Transmitted Wavefront Distortion:

Environmental & Durability Factors

ML-C-675A	Durability:
-----------	--------------------


Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
Lithuania	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- High Laser Damage Thresholds
- Excellent Surface Quality
- Insensitive to Input Beam's Polarization State

Laser Line Non-Polarizing Plate Beamsplitters are ideal for use in demanding laser applications where polarization control is critical. Laser Line Non-Polarizing Plate Beamsplitters are coated with dielectric layers to increase system performance while maintaining high laser damage thresholds and the polarization state of the input beam. The 1025nm – 1095nm coating is designed for some of the industry's most popular pulsed lasers, including Nd:YAG, Yb:KGW, and Yb:YAG.



Compatible Mounts

