

10.4" Diameter, 8.0" FL, Aspheric Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#32-595**

10 TO 12 DAYS

-

1

+

₹11,310.00

ADD TO CART

Qty 1-10
₹11,310.00
Qty 11+
₹9,875.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
264.16

Effective Focal Length EFL (mm):
203.20

Substrate:

Acrylic

Coating:

Uncoated
Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Diameter (inches): 10.4
Dimensional Tolerance (inches): ±0.05
Effective Diameter (inches): 10.0
Effective Focal Length EFL (inches): 8.00
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)
Typical Applications: Designed for finite conjugates of 4f (grooved side) and 4/3*f (flat side)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View