

TECHSPEC[®] 1050nm, 12.5mm Diameter, Dichroic Longpass Filter



Stock **#87-029** 1 In Stock

-

1

+

₹10,588

ADD TO CART

Volume Pricing	
Qty 1-5	₹10,588 each
Qty 6-25	₹8,408 each
Qty 26-49	₹7,785 each
Need More?	Request Quote

Product Downloads

General	
Dichroic Filter	Type:
Physical & Mechanical Properties	
12.50 +0.0/-0.1	Diameter (mm):
1.05 ±0.1	Thickness (mm):

Dimensional Tolerance (mm):	
+0.0/-0.2	
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2	
Optical Properties	
Angle of Incidence (°):	
45	
Cut-On Wavelength (nm):	
1,050.00	
Substrate: 	
Fused Silica (Corning 7980)	
Coating:	
Hard Coated	
Reflection (%):	
>97, Average Polarization >95, Absolute Polarization	
Reflection Wavelength (nm):	
790 - 1000	
Surface Quality:	
60-40	
Transmission (%):	
>85, Average Polarization >80, Absolute Polarization	
Transmission Wavelength (nm):	
1085 - 1600	
Transmitted Wavefront Tolerance:	
λ/4	
Cut-On Tolerance (%):	
±2	
Slope Factor (%):	
3.00	
Wavelength Range (nm):	
790 - 1600	
Wavelength Range (µm):	
0.79 - 1.6	

Environmental & Durability Factors	
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7	

Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	
Country of Origin:	
United States	
Imported By:	
Edmund Optics India Private Limited	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Fluorescence or Multispectral Imaging
- Sharp Cut-On Wavelength
- Broad Transmission and Reflection Ranges

Our TECHSPEC® Dichroic Longpass Filters are designed for a 45° angle of incidence. The rejected light is reflected at 90°, making these filters ideal for use in fluorescence applications or as spectral [beamsplitters](#). These hard coated filters feature low polarization dependence, broad spectral ranges, and a precision fused silica substrate. Reflection and transmission curves are available to easily integrate TECHSPEC® Dichroic Longpass Filters into any application.

Note: The chevron on the edge of the filter points towards surface S1 with the primary filter coating on which the light should be incident.

Hard coatings are used to increase durability while maintaining performance. The hard coating provides Dichroic Longpass Filters with high resistance to humidity, temperature, and abrasion, while also reducing the risk of damage when being handled.

Technical Information



Filter Type	Transmitted Wavefront (RMS)	Surface Quality	Surface Flatness (P-V)	R(avg)	T(avg)
HP Dichroic	$\lambda/10$	40-20	$\lambda/2$	>98%	>90%
Fluorescence Dichroics	1λ	60-40	-	>98%	>90%
Dichroic Longpass	$\lambda/4$	40-20	-	>97%	>85%

Compatible Mounts

;