

[See all 32 Products in Family](#)

10600nm, 8-12mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_CO2_Q-10

See More by [AdiOptica](#)



Stock #17-592 [CONTACT US](#)

1 MRP ₹4,93,223

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹4,93,223 each
Qty 5-10	₹4,43,518 each
Qty 11+	₹4,19,622 each
Need More?	Request Quote

Product Downloads

General

Model Number:
πShaper_CO2_Q-10

Type:

Compatible Adapter:

#12-322

Physical & Mechanical PropertiesLength (mm):
29.00Weight (g):
50Clear Aperture CA (mm):
20Diameter (mm):
42.00Input Beam Diameter, 1/e² (mm):
8 - 12**Optical Properties**Transmission (%):
>99Design Wavelength DWL (nm):
10600Wavelength Range (nm):
9000 - 11000Input Beam Mode:
TEM₀₀Typical Input Beam Mode Quality, M²:
<1.5Input Beam Divergence (mrad):
±20**Electrical**Maximum Input Power, CW (kW):
0.2**Threading & Mounting**Inner Thread:
M30 x 0.75Outer Thread:
M30 x 0.75**Regulatory Compliance**RoHS 2015:
CompliantCertificate of Conformance:
ViewReach 250:
CompliantCountry of Origin:
GermanyImported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000**Product Details**

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

