

[See all 21 Products in Family](#)

TECHSPEC® 100mm, M40 Mount, CA Series Fixed Focal Length Lens



100mm, M40 Mount, CA Series Fixed Focal Length Lens



Stock #29-263 **9 In Stock**

⊖ 1 ⊕ MRP ₹92,925

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹92,925 each
Need More?	Request Quote

Product Downloads

General

CA Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens **Imaging Lens Type:**

Physical & Mechanical Properties

Variable	Iris Option:
132.97	Length (mm):
61	Maximum Diameter (mm):
61	Outer Diameter (mm):
0	Maximum Rear Protrusion (mm):

Optical Properties

102.1mm - 12.7°	Horizontal Field of View, APS-C Sensor:
78.8mm - 9.8°	Horizontal Field of View, 4/3" Sensor:
64.7mm - 8.1°	Horizontal Field of View, 1.1" Sensor:
57.6mm - 7.3°	Horizontal Field of View, 1" Sensor:
40.1mm - 5.0°	Horizontal Field of View, 2/3" Sensor:
32.8mm - 4.1°	Horizontal Field of View, 1/1.8" Sensor:
28.8mm - 3.7°	Horizontal Field of View, 1/2" Sensor:
26.4mm - 3.3°	Horizontal Field of View, 1/2.5" Sensor:
21.9mm - 2.7°	Horizontal Field of View, 1/3" Sensor:
16.4mm - 2.1°	Horizontal Field of View, 1/4" Sensor:
27.90	Maximum Image Circle (mm):
0.0318	Numerical Aperture NA, Object Side:
8 (5)	Number of Elements (Groups):
100.00	Focal Length FL (mm):
500 - ∞	Working Distance (mm):
Horizontal: 101.7mm - 12.7° Vertical: 76.3mm - 9.6° Diagonal: 127.2mm - 15.9°	FOV @ Max Sensor Format, H x V (mm):
f/2.8 - f/22	Aperture (f/#):
λ/4 MgF ₂	Coating:
λ/4 MgF ₂	Coating Specification:
56.63	Entrance Pupil Position (mm):
48.89	Object Space Principal Plane (mm):
-51.79	Image Space Principal Plane (mm):
0.05	Maximum Distortion (%):
-44.61	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

APS-C	Maximum Sensor Format:
2.74	Pixel Size (μm):

Threading & Mounting

Filter Thread:

M46 x0.75 (Female)

Mount:

M40 x0.75

Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- APS-C (27.9mm), TFL-Mount Lens or M40 Mount Lens
- Greater than 30 MegaPixels, 3.45µm Pixel Size Sensors
- High Resolution, Compact APS-C Lens (CA)
- 35mm to 100mm Focal Length

TECHSPEC® CA (Compact APS) Series Fixed Focal Length Lenses are designed for high-resolution large-format sensors. Covering the APS-C format sensors with a 28mm image circle, these lenses feature a [TFL Mount](#) or M40 Mount. TFL Mounts feature an M35 x0.75 thread with a 17.5mm flange distance, and offer the same robustness and ease of use as a C-Mount. M40 Mounts feature a M52 x0.75 thread with a 17.526mm flange and provide a robust, large-format mounting solution ideal for high-resolution and larger image sensors with improved mechanical stability and optical performance compared to smaller format mounts. TECHSPEC® CA Series Fixed Focal Length Lenses offer a compact size while accommodating large format sensors, making them ideal for machine vision and [factory automation](#) applications.

These lenses won the [3rd place 2020 Inspect Award](#) and the [Silver-Level 2020 VSD Innovators Award](#).