

100μm 0.22 NA UV/VIS Fiber, 10m Length



Stock #57-067 10 TO 12 DAYS

-

1

+

₹4,176.00

ADD TO CART

Qty 1-4
₹4,176.00
Qty 5+
₹3,654.00
Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°):
25.4

Buffer Material:
Polyimide

Cladding Diameter (μm):
110 ±3

Coating: UVMS
Minimum Bend Radius (mm): 22/11 (Continuous/Momentary)
Substrate: Fused Silica (Coming 7980)
Length (m): 10.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 124 ±3
Core Diameter (µm): 100 ±3
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.439
Wavelength Range (nm): 190 - 1250
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View