

1064nm, 25.4mm Dia., 1x6 Spot Array, Diffractive Beamsplitter



HOLO/OR Diffractive Beamsplitters

Stock **#14-689** 10 TO 12 DAYS

⊖ 1 ⊕

₹155,295.00

ADD TO CART

Qty 1+
₹155,295.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 22.9
Coating: Laser V-Coat (1064nm)
Design Wavelength DWL (nm): 1064
Diameter (mm): 25.40 +0.05/-0.15
Substrate: Fused Silica (Coming 7980)

Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMor MM
Minimum Beam Diameter (mm): 0.48
Overall Efficiency (%): 82
Full Angle (°) : 3.8
Output Number of Spots: 6
Separation Angle (°): 0.76
Uniformity (%): <5
Zero Order, Relative to the Incident Beam (%): <1.5
Damage Threshold, Reference: See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant