

1064nm, 5.0mm Input, 3D Tophat Shaper



Stock #91-471 NEW 1 In Stock

-

1

+

MRP ₹5,64,117

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹5,64,117 each
Need More?	Request Quote

Product Downloads

Efficiency @ Design Wavelength DWL (%):
≥ 85%

General	
Beam Shaper	Type:
EDOF Flat Top	Style:

Physical & Mechanical Properties	
6.35 ±0.10mm	Thickness (mm):

25.00 +0.0mm/-0.1mm	Diameter (mm):
Optical Properties	
5.0	Entrance Beam Diameter, 1/e ² (mm):
±60% of Rayleigh Length	Focus Range (mm):
Fused Silica	Substrate: ☐
45	Angle of Incidence (°):
High Reflectivity	Coating:
1064	Design Wavelength DWL (nm):
1030 - 1064	Wavelength Range (nm):
HR coating, 1030 - 1064nm, 45°, R > 99.9%	Coating Specification:
TEM00 M ² ≤ 1.3	Input Beam Mode:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Stable Flat-Top Spots Across an Extended Axial Range
- High Efficiency with Low Side Lobes for Small-Spot Micromachining
- Depth-Of-Field Engineered Top-Hat (Flat-Top) Beam Shaping for Stable Industrial Processes
- Continuous Reflective DOE (Diffractive Optical Element) Based on a Micro-Structured Mirror
- Designed For Industrial Laser Systems from CW To Ultrashort Pulses

Mdel Photonics 3D Top-Hat Beam Shapers generate stable Flat-Top (Top-Hat) intensity profiles not only in the focal plane, but across an extended depth of field (EDOF). Unlike conventional beam shaping solutions that are highly sensitive to small focus or alignment changes, this extended depth-of-field engineered approach extends the usable process window and improves robustness in real production environments. The all-reflective design enables compact system layouts, supports high laser powers, and delivers reliable beam shaping performance for demanding industrial applications. Mdel Photonics 3D Top-Hat Beam Shapers are available in input beam diameters of 2.5, 5, and 8mm with multiple wavelength options and feature a ≥ 85% efficiency and an EDOF of ±60% of the Rayleigh length. These beam shapers are ideal for applications requiring precise and repeatable energy distribution such as laser precision marking, laser lift-off, precision drilling, wafer dicing, and surface micro-structuring.

Conventional Top-Hat solutions shape the beam mainly in the focus plane. In production, however, process stability depends on behavior across depth of field. 3D-Top-Hat Beam Shapers are designed to keep the top-hat stable over a defined axial range - extending the usable working range under realistic system conditions. At the core is a continuous reflective DOE (diffractive optical element) realized as a micro-structured mirror with a dielectric high-reflectivity coating. The result is a uniform Flat-Top spot with high efficiency and minimized side lobes.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools