

[See all 39 Products in Family](#)

**TECHSPEC® 101.6mm Dia. N/10 Fused Silica Optical Flat**



Stock #01-611-000 **9 In Stock**

MRP ₹92,819

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹92,819 each
Qty 6-10	₹82,730 each
Qty 11-25	₹77,181 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Interferometry Window **Type:**

**Physical & Mechanical Properties**

91.40 **Clear Aperture CA (mm):**

4.00 +0.00/-0.04	<b>Diameter (inches):</b>
101.60 +0.00/-1.00	<b>Diameter (mm):</b>
0.75 ±0.06	<b>Thickness (inches):</b>
19.05 ±1.5	<b>Thickness (mm):</b>
≤3	<b>Parallelism (arcmin):</b>
Protective as needed	<b>Bevel:</b>
Single Surface	<b>Construction:</b>
Fine Ground	<b>Edges:</b>
0.16	<b>Poisson's Ratio:</b>
73	<b>Young's Modulus (GPa):</b>
522.00	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>

## Optical Properties

Uncoated	<b>Coating:</b>
Clear	<b>Color:</b>
<a href="#">Fused Silica</a>	<b>Substrate:</b> <input type="checkbox"/>
1.458	<b>Index of Refraction (n<sub>d</sub>):</b>
60-40	<b>Surface Quality:</b>
67.8	<b>Abbe Number (v<sub>d</sub>):</b>
200 - 2200	<b>Wavelength Range (nm):</b>
λ10	<b>Surface Flatness (P-V):</b>

## Material Properties

2.20	<b>Density (g/cm<sup>3</sup>):</b>
0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Sizes Ranging from ½" Diameter to 14" Diameter
- Each λ/20 Flat 76.2mm and Larger Includes a Certificate of Calibration
- Available with Standard Metallic Mirror Coatings: [λ/10 and λ/20 Mirrors](#)

TECHSPEC® Single Surface Optical Flats are used as a reference (test plate) against which the flatness of an unknown surface may be compared. Each piece is precision polished by our master opticians and tested on a Zygo interferometer to insure the surface flatness. The secondary surfaces of our single surface flats are pitch polished to window quality for viewing the interference pattern. TECHSPEC Single Surface Optical Flats ship in a durable storage case for permanent protection. λ/20 flats that are 76.2mm or larger also include a certificate of calibration.

