

[See all 32 Products in Family](#)

1070nm, 18-23mm Dia. Input Beam, HP Sapphire Focal Flat Top Beam Shaper | Focal π Shaper_1070_Q-20_HP

See More by [AdiOptica](#)



Stock #17-594 **1 In Stock**

⊖ 1 ⊕ MRP ₹4,63,563

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹4,63,563 each
Qty 5-10	₹4,16,729 each
Qty 11+	₹3,93,790 each
Need More?	Request Quote

Product Downloads

General

Model Number:
πShaper_1070_Q-20_HP

Type:

Compatible Adapter:

#12-322

Physical & Mechanical Properties

Length (mm):

21.00

Weight (g):

70

Clear Aperture CA (mm):

38

Diameter (mm):

64.00

Input Beam Diameter, $1/e^2$ (mm):

18 - 23

Optical Properties

Transmission (%):

>99

Design Wavelength DWL (nm):

1070

Wavelength Range (nm):

1020 - 1100

Input Beam Mode:

TEM₀₀Typical Input Beam Mode Quality, M²:

<1.5

Input Beam Divergence (mrad):

±20

Electrical

Maximum Input Power, CW (kW):

5

Threading & Mounting

Inner Thread:

M58 x 1

Outer Thread:

M58 x 1

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 250:

Compliant

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

