

TECHSPEC® 10mm 30R/70T Cube Beamsplitter



Stock #68-547 **20+ In Stock**

- 1 + MRP ₹21,490

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹21,490 each
Qty 6-25	₹17,151 each
Qty 26-99	₹15,739 each
Need More?	Request Quote

Product Downloads

General

Standard Beamsplitter **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

Cube **Construction:**

	Dimensions (mm):
10.0 x 10.0 x 10.0 ±0.10	
Optical Properties	
	Beam Deviation (arcmin):
±3	
	Coating:
M/4 MgF ₂ @ 550nm on Faces Multilayer Dielectric on Hypotenuse	
	Reflection/Transmission Ratio (R/T):
30/70	
	Reflection/Transmission Tolerance (%):
±5	
	Substrate: <input type="checkbox"/>
N-BK7	
	Surface Quality:
60-40	
	Wavelength Range (nm):
400 - 700	
	Power (fringes) @ 632.8nm:
1.25	
	Irregularity (fringes) @ 632.8nm:
0.25	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Reach 223:
Compliant	
	Certificate of Conformance:
View	
	Country of Origin:
Singapore	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).



Product Details

- Multi-Layer Dielectric Coating
- Available in 30/70, 70/30, or 50/50 Split Ratios
- Optimal for Applications Insensitive to Polarization

TECHSPEC® Cube Beamsplitters are constructed by cementing two right angle prisms together and are offered in a range of reflection/transmission ratios. Output is partially polarized, making this product suitable for illumination and other applications where polarization is not a concern. TECHSPEC® Cube Beamsplitters feature an interference coating which is applied to the hypotenuse surface of one of the prisms to provide the designated reflection/transmission ratio with minimal absorption loss.

Note: If polarization sensitivity is critical to your application, we recommend using [TECHSPEC® Polarizing Beamsplitters](#) or [TECHSPEC® Non-Polarizing Beamsplitters](#).

Technical Information



;