

[See all 3 Products in Family](#)

# 1030nm Radial Polarization Converter



Stock **#89-449** [CONTACT US](#)

- 1 + MRP ₹4,85,786

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹4,85,786 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Polarization Converter **Type:**

### Physical & Mechanical Properties

6.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

3.00 ±0.1 **Thickness (mm):**

Dimensional Tolerance (mm):  
+0.0/-0.1

Construction:  
Self-Organized Nanogratings

## Optical Properties

Design Wavelength DWL (nm):  
1030

Substrate:   
Fused Silica (Corning 7980)

Surface Quality:  
20-10

Transmission (%):  
80-94 (wavelength dependent)

Wavelength Range (nm):  
995 - 1065

Surface Flatness (P-V):  
λ/8

Damage Threshold, By Design:   
20 J/cm<sup>2</sup> @ 1064nm, 3.5ns

## Regulatory Compliance

RoHS 2015:  
Compliant

Certificate of Conformance:  
View

Reach 247:  
Compliant

Country of Origin:  
Lithuania


Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Converts Linear Polarization to Radial or Azimuthal
- Converts Circular Polarization to an Optical Vortex (Donut-Shaped Beam)
- High Damage Thresholds in the Nano- and Femtosecond Range
- Higher-Order Versions Can Generate Higher Order Polarization Patterns and Optical Vortices

Radial Polarization Converters (S-waveplates) are space-variant retarders designed to convert linear polarization to radial or azimuthal polarization to reduce laser beam spot size. Alternatively, they can be used to convert circularly polarized light to an optical vortex (donut-shaped beam). The converters are manufactured by inscribing self-organized nanogratings inside fused silica using a femtosecond laser. Radial Polarization Converters (S-waveplates) are beneficial for a variety of polarization-sensitive applications. Radially polarized beams are highly efficient at micro-drilling high aspect-ratio features in metal, while vortex (donut-shaped) beams are ideal for STED or two-photon excitation fluorescence microscopy, laser micromachining, and optical tweezer applications (multiple particle trapping).

Higher Order Radial Polarization Converters (S-Waveplates) can generate higher order polarization patterns, optical vortices with increased topological charge, or vector Bessel beams when used in combination with [axicons](#). These types of beams are used in micromachining applications, such as microhole drilling of transparent materials.



## Technical Information

