

[See all 32 Products in Family](#)

1064nm, 11-17mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- π Shaper_1064_Q-14

See More by [AdlOptica](#)



#25-846: 1064nm, 11-17mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal- π Shaper_1064_Q-14



Stock **#25-846** [CONTACT US](#)

-

1

+

₹2,76,300

ADD TO CART

Volume Pricing	
Qty 1-4	₹2,76,300 each
Qty 5+	₹2,45,700 each
Need More?	Request Quote

Product Downloads

General	
Focal- π Shaper_1064_Q-14	Model Number:
Beam Shaper	Type:

Compatible Adapter:		#12-322
Physical & Mechanical Properties		
Length (mm):		29.00
Weight (g):		50
Clear Aperture CA (mm):		20
Diameter (mm):		42.00
Input Beam Diameter, 1/e ² (mm):		11 - 17
Optical Properties		
Transmission (%):		>99
Design Wavelength DWL (nm):		1064
Wavelength Range (nm):		1020 - 1100
Input Beam Mode:		TEM ₀₀
Typical Input Beam Mode Quality, M ² :		<1.5
Input Beam Divergence (mrad):		±20
Electrical		
Maximum Input Power, CW (kW):		0.3
Threading & Mounting		
Inner Thread:		M30 x0.75
Outer Thread:		M30 x0.75
Regulatory Compliance		
RoHS 2015:		Compliant
Certificate of Conformance:		View
Reach 250:		Compliant
Country of Origin:		Germany
Imported By:		Edmund Optics India Private Limited

Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica πShaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal-πShaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal-πShapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

Technical Information

