

[See all 81 Products in Family](#)

TECHSPEC® 10mm Dia. 320 - 450nm Broadband $\lambda/10$ Mirror



Stock **#37-559** **20+ In Stock**

⊖ 1 ⊕ MRP ₹12,612

● Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹12,612 each |
| Qty 6-25 | ₹10,089 each |
| Qty 26-49 | ₹9,459 each |
| Need More? | Request Quote |

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

10.00 +0.00/-0.20 **Diameter (mm):**

| | |
|---|--|
| 2.00 ±0.20 | Thickness (mm): |
| Commercial Polish | Back Surface: |
| 90 | Clear Aperture (%): |
| Ground, 0.5mm max bevel | Edges: |
| <0.5 | Parallelism (arcmin): |
| Optical Properties | |
| Dielectric | Coating Type: |
| Dielectric Mirror (320-450nm) | Coating: |
| λ/10 | Surface Flatness (P-V): |
| 320 - 450 | Wavelength Range (nm): |
| Fused Silica (Corning 7980) | Substrate: <input type="checkbox"/> |
| 0-45 | Angle of Incidence (°): |
| Coating Specification: R _{avg} >98% @ 340 - 488nm (0°, All Polarizations) R _{avg} >98% @ 320 - 450nm (45°, All Polarizations) R _{avg} >99% @ 320 - 450nm (45°, S-Polarization) | |
| 20-10 | Surface Quality: |
| Damage Threshold, By Design: <input type="checkbox"/> 0.5 J/cm ² @ 355nm, 20ns, 20Hz | |

| | |
|--|------------------------------------|
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 253: |
| United States | Country of Origin: |
| Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Enhanced Reflectivity and LIDT over Metallic Coatings
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Designed for all Polarization States from 0 – 45° AOI

TECHSPEC® Broadband Dielectric λ/10 Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric λ/10 Mirrors are designed for applications from the UV to the near-infrared spectra.

Technical Information



Compatible Mounts
