

TECHSPEC® 10mm Dia. x 20mm FL, NIR I Coated, Double-Convex Lens



Stock **#63-633** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹3,524.00

ADD TO CART

Qty 1-9
₹3,524.00
Qty 10+
₹3,176.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Back Focal Length BFL (mm):
19.16

Effective Focal Length EFL (mm): 20.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.25
Radius R₁=R₂ (mm): 20.24
Clear Aperture CA (mm): 9.00
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant