

TECHSPEC[®] 10mm Dia. x 100mm FL, VIS 0° Coated, Achromatic Lens



Stock #63-711 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹6,438.00

ADD TO CART

Qty 1-5
₹6,438.00
Qty 6+
₹5,155.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.025

Effective Focal Length EFL (mm):
100.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 98.16
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 9.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 4.00 ±0.10
Center Thickness CT 1 (mm) : 2.50 ±0.05
Center Thickness CT 2 (mm) : 1.50 ±0.05
Radius R₁ (mm) : 60.99
Radius R₂ (mm) : -43.74
Radius R₃ (mm) : -130.98
Edge Thickness ET (mm) : 3.70
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 10.00
Numerical Aperture NA : 0.05
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View