

**TECHSPEC® 10mm Dia. x 10mm FL, NIR II Coated, Double-Convex Lens**



Stock **#67-614-INK** 17 TO 22 D= DAYS

[Other Coating Options](#)

- 1 + **₹4,394.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| ₹4,394.00                     |
| Qty 10+                       |
| ₹3,959.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Diameter (mm):**  
10.00 ±0.025

**Back Focal Length BFL (mm):**  
8.89

|                                                                                                                                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Effective Focal Length EFL (mm):</b><br>10.00                                                                                                        |
| <b>Coating:</b><br>NIR II (750-1550nm)                                                                                                                  |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-SF5</a>                                                                                     |
| <b>Surface Quality:</b><br>40-20                                                                                                                        |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                                   |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                             |
| <b>Centering (arcmin):</b><br><1                                                                                                                        |
| <b>Center Thickness CT (mm):</b><br>3.50                                                                                                                |
| <b>Center Thickness Tolerance (mm):</b><br>±0.05                                                                                                        |
| <b>Edge Thickness ET (mm):</b><br>1.45                                                                                                                  |
| <b>Radius R<sub>1</sub>=R<sub>2</sub> (mm):</b><br>12.71                                                                                                |
| <b>Clear Aperture CA (mm):</b><br>9.00                                                                                                                  |
| <b>f#:</b><br>1.00                                                                                                                                      |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                                                                             |
| <b>Focal Length Tolerance (%):</b><br>±1.00                                                                                                             |
| <b>Numerical Aperture NA:</b><br>0.50                                                                                                                   |
| <b>Type:</b><br>Double-Convex Lens                                                                                                                      |
| <b>Wavelength Range (nm):</b><br>750 - 1550                                                                                                             |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>8 J/cm² @ 1064nm, 10ns                                                                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |