

TECHSPEC®

10mm Dia. x 50mm FL, NIR I Inked, Double-Convex Lens



Stock #63-637-INK 17 TO 22 D=DAYS

[Other Coating Options](#)



1



₹4,394.00

ADD TO CART

Qty 1-9
₹4,394.00
Qty 10+
₹3,959.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
10.00 ±0.025

Back Focal Length BFL (mm):
49.17

Effective Focal Length EFL (mm): 50.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.01
Radius R₁=R₂ (mm): 51.25
Clear Aperture CA (mm): 9.00
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View